

Rittal – The System.

Faster – better – everywhere.



AS 4050.780 Wire end ferrule

State: 7/15/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.780 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4050.780
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Blue
Length	12 mm 0.47 "
AWG	14
Internal diameter	4.2 mm 0.17 "
Rittal color code	Yes
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Customs tariff number	85369010
EAN	4028177999923
ETIM 9	EC000005
ETIM 8	EC000005

Features

ECLASS 8.0	36659290
------------	----------

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------