Rittal – The System.

Faster – better – everywhere.



AS 4050.783
Wire end ferrule

State: 11/22/2026 (Source: www.rittal.com/us-en)

AS 4050.783 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4050.783
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Gray
Length	12 mm 0.47 ″
AWG	12
Internal diameter	4.8 mm 0.19 ″
For cross section	4 mm²
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.210
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5 kg
Gross weight	0.5 kg
Customs tariff number	85369010
ETIM 9	EC000005

© Rittal 2026

Features

ETIM 8	EC000005
ECLASS 8.0	36659290
Product description	Wire end ferrules for wire assembly, 4 mm², AWG 12, gray, 12 mm, loose, 500 pieces

Approvals

Approvals	UL + C-UL (listed) UR