

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.785

## Wire end ferrule

State: 2/2/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))

# AS 4050.785 - Wire end ferrule Loose

With plastic collar.

## Features

Model No.	AS 4050.785
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Black
Length	12 mm 0.47 "
AWG	10
Internal diameter	6.3 mm 0.25 "
Rittal color code	Yes
For cross section	6 mm <sup>2</sup>
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.210
Delivery form	Loose
Packaging unit	100 pc(s).
Net weight	0.1
Gross weight	0.04
Customs tariff number	85369010
EAN	4028177815681

## Features

---

ETIM 9 EC000005

---

ETIM 8 EC000005

---

ECLASS 8.0 36659290

## Approvals

---

Approvals UL + C-UL (listed)  
UR