

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.105 Working light LED

State: 6/10/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.105 - Working light LED for WS 540

For attachment to the table top, with clamping device.



## Features

Model No.	AS 4051.105
Product description	For attachment to the table top, with clamping device.
Benefits	High-intensity, glare and flicker-free lighting, homogeneous and shadow-free Selectable color temperature between warm white, neutral white and daylight white promotes concentration and reduces fatigue Excellent color fidelity and strong contrast Aluminum spring arm with 3D head joint, swiveling and lockable for free positioning of light source
Technical specifications	Spring arm: length 970 mm Color rendering: 94–98 Ra Angle of projection: 100°
Material	Light enclosure: aluminum Glare reduction: Macrolon
Supply includes	Working light LED Assembly components
Rated power	26 W
Length of connection cable	3 m 118 "
Connection options	Plug-in power supply unit (CEE 7/16) with AC adapter
Light (bulb)	84 SMD LEDs

# Features

Protection category	III (SELV)
Luminous flux	2,930 lm
Suitable for Model No.	4051.100
Operating temperature range	-10 °C...40 °C 14 °F...104 °F
Rated operating voltage	110 V - 240 V, 1~, 50 Hz/60 Hz
Dimensions	Width: 545 mm Height: 90 mm Depth: 35 mm Width: 21.5 " Height: 3.54 " Depth: 1.38 "
Packaging unit	1 pc(s).
Net weight	2.5 kg
Gross weight	4.2 kg
Customs tariff number	94054990
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36629090
Product description	LED work light for WS 540, dimmable, 230 V/50 Hz