

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.536 Wire end ferrule

State: 8/2/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.536 - Wire end ferrule on belt

With plastic flange.

## Features

|                          |  |
|--------------------------|--|
| Model No.                | AS 4051.536  |
| Product description      | With plastic flange.   |
| Technical specifications | Heat resistant up to 105 °C  |
| Material                 | E-Cu, tin-plated<br>Plastic collar: Polypropylene                            |
| Color                    | Orange   |
| Length                   | 10 mm<br>0.39 ~  |
| AWG                      | 20   |
| Internal diameter        | 2.9 mm<br>0.11 ~   |
| Rittal color code        | Yes  |
| For cross section        | 0.5 mm <sup>2</sup>  |
| Multinorm                | Yes  |
| Note                     | UL-certified in conjunction with the relevant tools, e.g. crimping machines. |
| Delivery form            | Taped  |
| Packaging unit           | 4,000 pc(s).   |
| Customs tariff number    | 85369010   |
| EAN                      | 4028177937840  |
| ETIM 9                   | EC000005   |
| ETIM 8                   | EC000005   |
| ECLASS 8.0               | 36659290   |

# Approvals

---

Approvals

UL + C-UL (listed)