

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.541 Wire end ferrule

State: 7/7/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.541 - Wire end ferrule on belt

With plastic flange.

## Features

Model No.	AS 4051.541
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	White
Length	8 mm 0.31 "
AWG	18
Internal diameter	3.4 mm 0.13 "
Rittal color code	Yes
For cross section	0.75 mm <sup>2</sup>
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Delivery form	Taped
Packaging unit	4,000 pc(s).
Net weight	4 kg
Gross weight	0.58 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Features

---

Product description

Wire end ferrules 0.75 mm<sup>2</sup> x 8 mm AWG 18 multinorm, packs of 4,000 pc(s)., colour: white, delivery form: on belt (in accordance with the Rittal colour code), 0.75 mm<sup>2</sup>

# Approvals

---

Approvals

UL + C-UL (listed)