

Rittal – The System.

Faster – better – everywhere.



AS 4051.543 Wire end ferrule

State: 7/1/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.543 - Wire end ferrule on belt

With plastic flange.

Features

Model No.	AS 4051.543
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Red
Length	8 mm 0.31 "
AWG	16
Internal diameter	4 mm 0.16 "
Rittal color code	Yes
For cross section	1.5 mm ²
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Delivery form	Taped
Packaging unit	4,000 pc(s).
Net weight	4 kg
Gross weight	0.64 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Features

Product description

Wire end ferrules 1.5 mm² x 8 mm AWG 16 multinorm, packs of 4,000 pc(s)., colour: red, delivery form: on belt (in accordance with the Rittal colour code), 1.5 mm²

Approvals

Approvals

UL + C-UL (listed)