Rittal – The System.

Faster – better – everywhere.





AS 4051.544 Wire end ferrule

State: 10/28/2025 (Source: rittal.com/us-en)



AS 4051.544 - Wire end ferrule on belt

With plastic flange.

Features

Model No.	AS 4051.544
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	White
Length	10 mm 0.39 <i>"</i>
AWG	20
Internal diameter	2.9 mm 0.11 "
For cross section	0.5 mm²
DIN color code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Delivery form	Taped
Packaging unit	4,000 pc(s).
Net weight	4
Customs tariff number	85369010
EAN	4028177937925
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

© Rittal 2025

Approvals

Approvals

UL + C-UL (listed)

© Rittal 2025 3