


# Rittal – The System.

Faster – better – everywhere.



## AS 4051.546

### Wire end ferrule

State: 8/2/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.546 - Wire end ferrule on belt

With plastic flange.

## Features

Model No.	AS 4051.546
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Red
Length	10 mm 0.39 ~
AWG	18
Internal diameter	3.5 mm 0.14 ~
For cross section	1 mm <sup>2</sup>
DIN color code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Delivery form	Taped
Packaging unit	4,000 pc(s).
Customs tariff number	85369010
EAN	4028177937949
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Approvals

---

Approvals

UL + C-UL (listed)