

Rittal – The System.

Faster – better – everywhere.



AS 4051.549 Wire end ferrule

State: 4/26/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.549 - Wire end ferrule on belt

With plastic flange.

Features

Model No.	AS 4051.549
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Gray
Length	8 mm 0.31 "
AWG	18
Internal diameter	3.4 mm 0.13 "
For cross section	0.75 mm ²
DIN color code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Delivery form	Taped
Packaging unit	4,000 pc(s).
Net weight	4 kg
Gross weight	0.543 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Features

Product description	Wire end ferrules 0.75 mm ² x 8 mm AWG 18 multinorm, packs of 4,000 pc(s)., colour: grey, delivery form: on belt (in accordance with the DIN colour code), 0.75 mm ²
---------------------	--

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------