



# AS 4051.551 - Wire end ferrule on belt

With plastic flange.

## Features

Model No.	AS 4051.551
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Black
Length	8 mm 0.31 "
AWG	16
Internal diameter	4 mm 0.16 "
For cross section	1.5 mm <sup>2</sup>
DIN color code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Delivery form	Taped
Packaging unit	4,000 pc(s).
Net weight	4 kg
Gross weight	0.645 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Features

---

Product description

Wire end ferrules 1.5 mm<sup>2</sup> x 8 mm AWG 16 multinorm, packs of 4,000 pc(s)., colour: black, delivery form: on belt (in accordance with the DIN colour code), 1.5 mm<sup>2</sup>

# Approvals

---

Approvals

UL + C-UL (listed)