Rittal – The System.

Faster - better - everywhere.





AS 4051.580 Wire end ferrule

State: 11/23/2025 (Source: rittal.com/us-en)



AS 4051.580 - Wire end ferrule Loose

With plastic collar.

Features

| Model No. | AS 4051.580 |
|--------------------------|--|
| Product description | With plastic collar. |
| Technical specifications | Heat resistant up to 105 °C |
| Material | E-Cu, tin-plated |
| | Plastic collar: Polypropylene |
| Color | Yellow |
| Length | 8 mm |
| | 0.31 ″ |
| AWG | 18 |
| Internal diameter | 3.5 mm |
| | 0.14 ″ |
| Rittal color code | Yes |
| Multinorm | Yes |
| Note | UL-certified in conjunction with the relevant tools, e.g. crimping |
| | machines. |
| | For tailored advice, please contact a Rittal representative. |
| Delivery form | Loose |
| Packaging unit | 500 pc(s). |
| Net weight | 0.5 |
| Customs tariff number | 85369010 |
| EAN | 4028177999787 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |
| | |

© Rittal 2025

Approvals

Approvals

UL + C-UL (listed)

UR

© Rittal 2025 3