Rittal – The System.

Faster – better – everywhere.



AS 4051.582
Wire end ferrule

State: 11/15/2026 (Source: www.rittal.com/us-en)

AS 4051.582 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4051.582
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Yellow
Length	12 mm 0.47 ″
AWG	18
Internal diameter	3.5 mm 0.14 ″
Rittal color code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Product description	Wire end sleeves for wire assembly, 1.0 mm², yellow, loose, 12 mm

© Rittal 2026

Approvals

Approvals	UL + C-UL (listed) UR