Rittal – The System.

Faster – better – everywhere.



AS 4051.604

Wire end ferrule

State: 11/5/2026 (Source: www.rittal.com/us-en)

AS 4051.604 - Wire end ferrule on belt

With plastic flange.

Features

Model No.	AS 4051.604
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Red
Length	10 mm 0.39 ″
AWG	16
Internal diameter	3.5 mm 0.14 ″
Rittal color code	Yes
For cross section	1.5 mm²
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packaging unit	5,000 pc(s).
Net weight	5 kg
Gross weight	0.794 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

© Rittal 2026

Features

Product description	Wire end ferrules 1.5 mm² x 10 mm AWG 16, packs of 5,000 pc(s)., colour: red, delivery form: on belt (in accordance with the Rittal colour code)

Approvals

Approvals	UL + C-UL (listed)