

Rittal – The System.

Faster – better – everywhere.



AS 4051.624 Wire end ferrule

State: 4/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.624 - Wire end ferrule Loose

With plastic collar.

Features

| | |
|--------------------------|--|
| Model No. | AS 4051.624 |
| Product description | With plastic collar. |
| Technical specifications | Heat resistant up to 105 °C |
| Material | E-Cu, tin-plated Plastic collar: Polypropylene |
| Color | Black |
| Length | 18 mm 0.71 " |
| AWG | 16 |
| Internal diameter | 3.5 mm 0.14 " |
| DIN color code | Yes |
| Note | UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative. |
| Standards | AEH DIN 46228 |
| Delivery form | Loose |
| Packaging unit | 500 pc(s). |
| Net weight | 0.5 |
| Customs tariff number | 85369010 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |
| Product description | Wire end sleeves for wire assembly, 1.5 mm ² , black, loose, 18 mm |

Approvals

Approvals

UL + C-UL (listed)

UR