## Rittal – The System.

Faster - better - everywhere.





# AS 4051.644 Wire end ferrule

State: 11/1/2025 (Source: rittal.com/us-en)



## AS 4051.644 - Wire end ferrule Loose

With plastic collar.

#### **Features**

Model No.	AS 4051.644	
Product description	With plastic collar.	
Technical specifications	Heat resistant up to 105 °C	
Material	E-Cu, tin-plated Plastic collar: Polypropylene	
Color	Red	
Length	10 mm 0.39 ″	
AWG	18	
Internal diameter	3 mm 0.12 ″	
For cross section	1 mm²	
DIN color code	Yes	
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.	
Standards	AEH DIN 46228	
Suitable for Model No.	4051.205 4051.210	
Delivery form	Loose (10 packs of 100)	
Packaging unit	1,000 pc(s).	
Net weight	1	
Customs tariff number	85369010	
EAN	4028177815858	

© Rittal 2025

## **Features**

ETIM 9	EC000005	
ETIM 8	EC000005	
ECLASS 8.0	36659290	

# **Approvals**

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3