

Rittal – The System.

Faster – better – everywhere.



AS 4051.683

Wire end ferrule

State: 2/8/2026 (Source: rittal.com/us-en)

AS 4051.683 - Wire end ferrule Loose

With plastic collar.

Features

| | |
|--------------------------|--|
| Model No. | AS 4051.683 |
| Product description | With plastic collar. |
| Technical specifications | Heat resistant up to 105 °C |
| Material | E-Cu, tin-plated Plastic collar: Polypropylene |
| Color | White |
| Length | 12 mm 0.47 " |
| AWG | 20 |
| Internal diameter | 2.9 mm 0.11 " |
| DIN color code | Yes |
| Multinorm | Yes |
| Note | UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative. |
| Delivery form | Loose |
| Packaging unit | 500 pc(s). |
| Net weight | 0.5 |
| Gross weight | 0.047 |
| Customs tariff number | 85369010 |
| EAN | 4028177999602 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |

Features

ECLASS 8.0 36659290

Approvals

Approvals UL + C-UL (listed)
UR