Rittal – The System.

Faster - better - everywhere.





AS 4051.687 Wire end ferrule

State: 11/15/2025 (Source: rittal.com/us-en)



AS 4051.687 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4051.687
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Red
Length	12 mm 0.47 ″
AWG	18
Internal diameter	3.5 mm 0.14 ″
DIN color code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Delivery form	Loose
Packaging unit	500 pc(s).
Net weight	0.5
Gross weight	0.063
Customs tariff number	85369010
EAN	4028177999824
ETIM 9	EC000005
ETIM 8	EC000005

© Rittal 2025

Features

ECLASS 8.0 36659290

Approvals

Approvals UL + C-UL (listed) UR

© Rittal 2025

3