Rittal – The System.

Faster – better – everywhere.



# AS 4051.719
# Wire end ferrule

State: 10/31/2026 (Source: www.rittal.com/us-en)

# AS 4051.719 - Wire end ferrule Loose

With plastic collar.

## Features

| | |
|---|---|
| Model No. | AS 4051.719 |
| Product description | With plastic collar. |
| Technical specifications | Heat resistant up to 105 °C |
| Material | E-Cu, tin-plated<br>Plastic collar: Polypropylene |
| Color | Light blue |
| Length | 12 mm<br>0.47 ″ |
| AWG | 18 |
| Internal diameter | 2.8 mm<br>0.11 ″ |
| DIN color code | Yes |
| Note | UL-certified in conjunction with the relevant tools, e.g. crimping machines.<br>For tailored advice, please contact a Rittal representative. |
| Standards | AEH DIN 46228 |
| Delivery form | Loose |
| Packaging unit | 500 pc(s). |
| Net weight | 0.5 |
| Customs tariff number | 85369010 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |

© Rittal 2026

# Features

| | |
|---|---|
| Product description | Wire end sleeves for wire assembly 0.75 mm², light blue, loose, 12 mm |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed)<br>UR |