

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.728 Wire end ferrule

State: 5/27/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.728 - Wire end ferrule Loose

With plastic collar.

## Features

|                          |  |
|--------------------------|--|
| Model No.                | AS 4051.728  |
| Product description      | With plastic collar.   |
| Technical specifications | Heat resistant up to 105 °C  |
| Material                 | E-Cu, tin-plated<br>Plastic collar: Polypropylene  |
| Color                    | Orange   |
| Length                   | 10 mm<br>0.39 "  |
| AWG                      | 12   |
| Internal diameter        | 4.8 mm<br>0.19 "   |
| DIN color code           | Yes  |
| Note                     | UL-certified in conjunction with the relevant tools, e.g. crimping machines.<br>For tailored advice, please contact a Rittal representative. |
| Standards                | AEH DIN 46228  |
| Delivery form            | Loose  |
| Packaging unit           | 500 pc(s).   |
| Net weight               | 0.5  |
| Customs tariff number    | 85369010   |
| ETIM 9                   | EC000005   |
| ETIM 8                   | EC000005   |
| ECLASS 8.0               | 36659290   |
| Product description      | Wire end sleeves for wire assembly, 4.0 mm <sup>2</sup> , orange, loose, 10 mm   |

# Approvals

---

Approvals

UL + C-UL (listed)

UR