Rittal – The System.

Faster – better – everywhere.



# AS 4051.730
# Wire end ferrule

State: 11/2/2026 (Source: www.rittal.com/us-en)

# AS 4051.730 - Wire end ferrule Loose

With plastic collar.

## Features

| | |
|---|---|
| Model No. | AS 4051.730 |
| Product description | With plastic collar. |
| Technical specifications | Heat resistant up to 105 °C |
| Material | E-Cu, tin-plated<br>Plastic collar: Polypropylene |
| Color | Orange |
| Length | 18 mm<br>0.71 ″ |
| AWG | 12 |
| Internal diameter | 4.8 mm<br>0.19 ″ |
| DIN color code | Yes |
| Note | UL-certified in conjunction with the relevant tools, e.g. crimping machines.<br>For tailored advice, please contact a Rittal representative. |
| Standards | AEH DIN 46228 |
| Delivery form | Loose |
| Packaging unit | 100 pc(s). |
| Net weight | 0.1 |
| Customs tariff number | 85369010 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |
| Product description | Wire end sleeves for wire assembly, 4.0 mm², orange, loose, 18 mm |

© Rittal 2026

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed)<br>UR |