Rittal – The System.

Faster – better – everywhere.



AS 4051.732
Wire end ferrule

State: 11/5/2026 (Source: www.rittal.com/us-en)

AS 4051.732 - Wire end ferrule Loose

With plastic collar.

Features

Model No.	AS 4051.732
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Length	18 mm 0.71 ″
AWG	10
Internal diameter	6.3 mm 0.25 ″
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Delivery form	Loose
Packaging unit	100 pc(s).
Net weight	0.1
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Product description	Wire end sleeves for wire assembly, 6.0 mm², green, loose, 18 mm

© Rittal 2026

Approvals

Approvals	UL + C-UL (listed) UR