


# Rittal – The System.

Faster – better – everywhere.



# AS 4052.122

## Screwdriver

State: 12/5/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4052.122 - Screwdriver Insulated

With a long, slender handle and high-performance tip with insulation.

## Features

Model No.	AS 4052.122
Version	With 1000 V protective insulation For Pozidriv recessed head
Product description	With a long, slender handle and high-performance tip with insulation.
Benefits	Minimal force required, thanks to ergonomically styled handle Handle head with roll-off protection and clear screw marking Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than that of a comparable tool Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working
Material	Blade: Chromium molybdenum vanadium alloy Inside of handle: Hard plastic Handle body: elastic, highly flexible plastic
Color	Handle: Anthracite and Rittal Power Pink
Blade dia.	6 mm
Blade length	100 mm
Output	PZ 2
Handle dia.	27 mm
Handle length	115 mm
Standards	IEC 60 900
Packaging unit	3 pc(s).
Customs tariff number	82054000
EAN	4028177807266
ETIM 9	EC000144

# Features

ETIM 8	EC000144
ECLASS 8.0	21040406