

Rittal – The System.

Faster – better – everywhere.



AS 4054.020 Crimping pliers

State: 12/25/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.020 - Crimping pliers For cable lugs

For use with non-insulated ring terminals



Features

Model No.	AS 4054.020
Version	Angled
Product description	For crimping non-insulated ring terminals.
Benefits	Unlockable forced lock Thanks to optimized lever transmission, only minimal actuation forces are required even for larger cross-sections
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Indent crimp
Dimensions	Height: 59 mm Length: 198 mm Height: 2.32 " Length: 7.8 "
AWG	20 - 14
For cross section	0.5 - 2.5 mm ²
Packaging unit	1 pc(s).
Net weight	0.429
Gross weight	0.439

Features

Customs tariff number	82032000
EAN	4028177807624
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811