

Rittal – The System.

Faster – better – everywhere.



AS 4054.021

Crimping pliers

State: 2/13/2026 (Source: ittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.021 - Crimping pliers For cable lugs

For use with non-insulated ring terminals



Features

Model No.	AS 4054.021
Version	Angled
Product description	For crimping non-insulated ring terminals.
Benefits	Unlockable forced lock Thanks to optimized lever transmission, only minimal actuation forces are required even for larger cross-sections
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Indent crimp
Dimensions	Height: 59 mm Length: 198 mm Height: 2.32 " Length: 7.8 "
AWG	22 - 10
For cross section	0.35 - 6 mm ²
Packaging unit	1 pc(s).
Net weight	0.425
Gross weight	0.435

Features

Customs tariff number 82032000

EAN 4028177807631

ETIM 9 EC000168

ETIM 8 EC000168

ECLASS 8.0 21043811