Rittal – The System.

Faster - better - everywhere.





AS 4054.140 Crimper

State: 10/31/2025 (Source: rittal.com/us-en)



AS 4054.140 - Crimper For cable lugs

For use with insulated ring terminals and connectors



Features

Model No.	AS 4054.140
Version	Angled
Product description	For crimping insulated ring terminals and connectors.
Benefits	Clear assignment of cross section through color coding on the dies Unlockable forced lock
	Releases as soon as the required pressure is reached, to prevent ramming
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Oval crimp
Dimensions	Height: 59 mm
	Length: 198 mm
	Height: 2.32 "
	Length: 7.8 ″
AWG	22 - 14
For cross section	0.75 - 2.5 mm²
Packaging unit	1 pc(s).
Net weight	0.42
Gross weight	0.44

© Rittal 2025

Features

Customs tariff number	82032000
EAN	4028177807686
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811

© Rittal 2025 3