

Rittal – The System.

Faster – better – everywhere.



AS 4055.020 Manual hydraulic punch

State: 6/15/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.020 - Manual hydraulic punch

For punching round, square and rectangular cut-outs.



Features

| | |
|-----------------------|---|
| Model No. | AS 4055.020 |
| Version | Flexible, with hydraulic hose and separate cylinder |
| Product description | For punching round, square and rectangular openings. |
| Benefits | Extend tool life with a built-in pressure relief valve |
| Material | Aluminum |
| Supply includes | Manual hydraulic punch Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5/19 mm HSS pilot drill Ø 11 mm Spacer bushing set (3-part) Plastic case |
| Hydraulic operation | Round hole punch up to Ø 82 mm Rectangular hole punch up to 46 x 86 mm Punching force 75 kN Max. operating pressure 680 bar/9850 psi Square knockout punch up to 92 x 92 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 3.4 kg |
| Gross weight | 3.546 kg |
| Customs tariff number | 84678900 |
| ETIM 9 | EC001085 |

Features

| | |
|---------------------|---------------------------------------|
| ETIM 8 | EC001085 |
| ECLASS 8.0 | 21049046 |
| Product description | Hand hydraulic punch, hose a. cylind. |
