

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.085**

**Manual hydraulic punch set, PG 9 -  
PG 48**

State: 5/12/2024 (Source: [rittal.com/us-en](https://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.085 - Manual hydraulic punch set, PG 9 - PG 48

Manual hydraulic punch in a practical set with hole punches

## Features

Model No.	AS 4055.085
Version	With cylinder head offset at 90° and rotatable through 360°
Product description	Manual hydraulic punch set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.
Benefits	Extend tool life with a built-in pressure relief valve
Supply includes	Manual hydraulic punch 9 split sheet metal punch with 3-fold pitch Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5/19 mm HSS pilot drill Ø 10 mm Spacer bushing set (3-part) Plastic case
Max. material thickness that can be machined for sheet steel	2 mm 2 mm 2 mm 2 mm 2 mm 3 mm 3 mm 3 mm 3 mm
Ø hole punch	15.2 mm 18.6 mm 20.4 mm 22.5 mm 28.3 mm 37 mm 47 mm 54 mm 60 mm
Packaging unit	1 pc(s).

# Features

Weight/packaging unit	5.85 kg 12.9 lb.
Customs tariff number	84678900
EAN	4028177807969
ETIM 7.0	EC001085
ECLASS 8.0	21049046