Rittal – The System.

Faster – better – everywhere.



SZ 4127.210
Door-Operated Switch

State: 11/22/2026 (Source: www.rittal.com/us-en)

SZ 4127.210 - Door-Operated Switch

With mounting accessories, with or without connection cable.

Features

Model No.	SZ 4127.210
Version	with toggle for swing frame, without connection cable
Function principle	The toggle is actuated via the tubular door frame of the Carbon steel door, or in the case of glazed doors, via an adapter included with the supply.
Note	For installation in VX IT only in conjunction with VX mounting bracket for door-operated switch.
Rated impulse withstand voltage, phase to phase	6000 V AC
Rated insulation voltage	400 V AC
Installation options	for TS enclosures with installed large swing frame for standard and courtesy lights
Electrical connection	240 V AC/6 A 125 V DC/8 A 24 V AC/6 A 24 V DC/6 A
Rated operating voltage	400 V
Protection category IP to IEC 60 529	IP 40
Packaging unit	1 pc(s).
Net weight	0.231 kg
Gross weight	0.235 kg
Customs tariff number	85365019
ETIM 9	EC002626
ETIM 8	EC002626
ECLASS 8.0	27189266

© Rittal 2026

Features

Product description	SZ Door-operated switch, with toggle, without connection cable, UL

Approvals

Approvals	CQC CQC-CCC CSA UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2026