Rittal – The System.

Faster - better - everywhere.





SZ 4138.190 Standard light

State: 11/25/2025 (Source: rittal.com/us-en)



SZ 4138.190 - Standard light

Supply voltage: 120 V AC 60 Hz, 230 V AC 50 Hz

Features

| Model No. | SZ 4138.190 |
|---|---|
| Version | with door-operated switch |
| Supply includes | Standard light Light (bulb) Assembly components Integral door-operated switch |
| Rated power | 18 W |
| Ballast | Magnetic ballast |
| Connection options | Power supply through connector Through-wiring (configuration of row of luminaires) |
| Integral door-operated switch | Yes |
| Light (bulb) | Fluorescent lamp, G13 backplate |
| Protection category | I (PE conductor) |
| Switch (type) | Integrated, on/off/door-operated switch |
| Light – installation type | Screw fastening |
| Rated impulse withstand voltage, phase to earth | 1500 V AC |
| Rated impulse withstand voltage, phase to phase | 500 V AC |
| Rated insulation voltage | 500 V DC/1s |
| Installation options | TS horizontal profile from roof frames: direct TS, SE vertical section: with TS adapter bracket SE sections on front and rear of roof frame: with TS adapter bracket SE profiles to the side of roof frames: direct |

© Rittal 2025

Features

| Dimensions | Width: 682 mm |
|-----------------------------|-------------------------------------|
| | Height: 117 mm |
| | Depth: 50 mm |
| | Width: 26.9 " |
| | Height: 4.61 " |
| | Depth: 1.97 " |
| Operating temperature range | -15 °C45 °C |
| | 5 °F113 °F |
| Outlets | D, ground contact (type F, CEE 7/4) |
| Storage temperature range | -20 °C70 °C |
| | -4 °F158 °F |
| Rated operating voltage | 230 V, 1~, 50 Hz |
| Socket version | D, ground contact (type F, CEE 7/4) |
| Packaging unit | 1 pc(s). |
| Net weight | 2.02 |
| Gross weight | 2.22 |
| Customs tariff number | 94054990 |
| EAN | 4028177320727 |
| ECLASS 8.0 | 27189241 |
| | |

Approvals

| Explanations | Declaration of conformity |
|--------------|------------------------------|
| | Declaration of conformity UK |

© Rittal 2025 3