Rittal – The System.

Faster – better – everywhere.





SZ 4138.300 Standard light

State: 11/18/2025 (Source: rittal.com/us-en)



SZ 4138.300 - Standard light

Supply voltage: 120 V AC 60 Hz, 230 V AC 50 Hz

Features

Model No.	SZ 4138.300
Version	without door-operated switch
Supply includes	Standard light Light (bulb) Assembly components
Rated power	30 W
Ballast	Magnetic ballast
Connection options	Door-operated switch Power supply through connector Through-wiring (configuration of row of luminaires)
Light (bulb)	Fluorescent lamp, G13 backplate
Protection category	I (PE conductor)
Switch (type)	Integrated, on/off/door-operated switch
Light – installation type	Screw fastening
Rated impulse withstand voltage, phase to earth	1500 V AC
Rated impulse withstand voltage, phase to phase	1000 V AC
Rated insulation voltage	500 V DC/1s
Installation options	TS horizontal profile from roof frames: direct TS, SE vertical section: with TS adapter bracket SE sections on front and rear of roof frame: with TS adapter bracket SE profiles to the side of roof frames: direct AE, CM, TP: with universal bracket AE: with rail for interior installation

© Rittal 2025

Features

Dimensions	Width: 987 mm
	Height: 117 mm
	Depth: 50 mm
	Width: 38.9 "
	Height: 4.61 "
	Depth: 1.97 "
Operating temperature range	-15 °C45 °C
	5 °F113 °F
Outlets	D, ground contact (type F, CEE 7/4)
Storage temperature range	-20 °C70 °C
	-4 °F158 °F
Rated operating voltage	230 V, 1~, 50 Hz
Socket version	D, ground contact (type F, CEE 7/4)
Packaging unit	1 pc(s).
Net weight	2.8
Gross weight	3
Customs tariff number	94054990
EAN	4028177092297
ECLASS 8.0	27189241

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3