

# Rittal – The System.

Faster – better – everywhere.



## SZ 4139.150 Courtesy light

State: 1/1/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 4139.150 - Courtesy light

Supply voltage: 100 - 240 V AC 50/60 Hz

## Features

|   |  |
|---|--|
| Model No.                                       | SZ 4139.150  |
| Version   | with door-operated switch  |
| Supply includes                                 | Courtesy light<br>Light (bulb)<br>Light cover<br>Assembly components<br>Integral door-operated switch  |
| Rated power                                     | 14 W   |
| Ballast   | Wide range voltage EB  |
| Connection options                              | Power supply through connector<br>Through-wiring (configuration of row of luminaires)  |
| Integral door-operated switch                   | Yes  |
| Light (bulb)                                    | Fluorescent lamp, G13 backplate  |
| Protection category                             | I (PE conductor)   |
| Switch (type)                                   | Integrated, on/off/door-operated switch  |
| Light cover                                     | Yes  |
| Light – installation type                       | Screw fastening  |
| Rated impulse withstand voltage, phase to earth | 1000 V AC  |
| Rated impulse withstand voltage, phase to phase | 500 V AC   |
| Rated insulation voltage                        | 500 V DC/1s  |
| Installation options                            | TS horizontal profile from roof frames: direct<br>TS, SE vertical section: with TS adapter bracket<br>SE sections on front and rear of roof frame: with TS adapter bracket<br>SE profiles to the side of roof frames: direct |

# Features

|                             |   |
|-----------------------------|---|
| Dimensions                  | Width: 452 mm<br>Height: 117 mm<br>Depth: 50 mm<br>Width: 17.8 "<br>Height: 4.61 "<br>Depth: 1.97 " |
| Operating temperature range | -15 °C...45 °C<br>5 °F...113 °F   |
| Outlets                     | D, ground contact (type F, CEE 7/4)   |
| Storage temperature range   | -20 °C...70 °C<br>-4 °F...158 °F  |
| Rated operating voltage     | 100 V - 240 V, 1~, 50 Hz/60 Hz  |
| Socket version              | D, ground contact (type F, CEE 7/4)   |
| Packaging unit              | 1 pc(s).  |
| Net weight                  | 1.25  |
| Gross weight                | 1.319   |
| Customs tariff number       | 94054990  |
| EAN                         | 4028177320741   |
| ECLASS 8.0                  | 27189241  |

# Approvals

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|