## Rittal - The System.

Faster - better - everywhere.





# SZ 4139.180 Courtesy light

State: 11/29/2025 (Source: rittal.com/us-en)



## SZ 4139.180 - Courtesy light

Supply voltage: 100 - 240 V AC 50/60 Hz

#### **Features**

Model No.	SZ 4139.180
Version	without door-operated switch
Supply includes	Courtesy light Light (bulb) Light cover Assembly components
Rated power	18 W
Ballast	Wide range voltage EB
Connection options	Power supply through connector Door-operated switch Through-wiring (configuration of row of luminaires)
Light (bulb)	Fluorescent lamp, G13 backplate
Protection category	I (PE conductor)
Switch (type)	Integrated, on/off/door-operated switch
Light cover	Yes
Light – installation type	Screw fastening
Rated impulse withstand voltage, phase to earth	1000 V AC
Rated impulse withstand voltage, phase to phase	500 V AC
Rated insulation voltage	500 V DC/1s
Installation options	TS horizontal profile from roof frames: direct TS, SE vertical section: with TS adapter bracket SE sections on front and rear of roof frame: with TS adapter bracket SE profiles to the side of roof frames: direct AE, CM, TP: with universal bracket AE: with rail for interior installation

© Rittal 2025 2

### Features

Dimensions	Width: 682 mm
	Height: 117 mm
	Depth: 50 mm
	Width: 26.9 "
	Height: 4.61 "
	Depth: 1.97 "
Operating temperature range	-15 °C45 °C
	5 °F113 °F
Outlets	D, ground contact (type F, CEE 7/4)
Storage temperature range	-20 °C70 °C
	-4 °F158 °F
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Socket version	D, ground contact (type F, CEE 7/4)
Packaging unit	1 pc(s).
Net weight	1.55
Gross weight	1.8
Customs tariff number	94054990
EAN	4028177092341
ECLASS 8.0	27189241

## Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3