
Rittal - The System.

Faster - better - everywhere.





SZ 4315.320 Door-Operated Switch

State: 11/24/2025 (Source: rittal.com/us-en)



SZ 4315.320 - Door-Operated Switch

With mounting accessories, with or without connection cable.

Features

| Model No. | SZ 4315.320 |
|--|---|
| Version | With connection cable |
| Length | 1,000 mm 39.4 ″ |
| Rated impulse withstand voltage, phase to phase | 6000 V AC |
| Rated insulation voltage | 400 V AC |
| Installation options | for standard and courtesy lights without an integrated door- operated switch |
| Dimensions | Length: 1,000 mm Length: 39.4 " |
| Electrical connection | 240 V AC/6 A 125 V DC/8 A 24 V AC/6 A 24 V DC/6 A |
| Rated operating voltage | 400 V |
| Protection category IP to IEC 60 529 | IP 40 |
| Packaging unit | 1 pc(s). |
| Net weight | 0.139 |
| Gross weight | 0.149 |
| Customs tariff number | 85365019 |
| EAN | 4028177581333 |
| ETIM 9 | EC002626 |
| ETIM 8 | EC002626 |

© Rittal 2025

Features

| SS 8.0 27189266 |
|-----------------|

Approvals

| Approvals | CQC CQC-CCC |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |

© Rittal 2025 3