

Faster – better – everywhere.



State: 7/17/2025 (Source: rittal.com/us-en)



► SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SZ 4315.710 - Door-Operated Switch

With mounting accessories, with or without connection cable.

Features

Model No.	SZ 4315.710
Version	With connection cable
Length	600 mm 23.6 "
Rated impulse withstand voltage, phase to phase	6000 V AC
Rated insulation voltage	400 V AC
Installation options	for compact lights
Dimensions	Length: 600 mm Length: 23.6 "
Electrical connection	240 V AC/2.5 A 125 V DC/2.5 A 24 V AC/2.5 A 24 V DC/2.5 A
Rated operating voltage	400 V
Protection category IP to IEC 60 529	IP 40
Packaging unit	1 pc(s).
Net weight	0.11
Gross weight	0.139
Customs tariff number	85365019
EAN	4028177581371
E-Number Sweden	E3404495
ETIM 9	EC002626
ETIM 8	EC002626

Features

ECLASS 8.0	27189266
------------	----------

Approvals

Approvals	CQC CQC-CCC
-----------	----------------

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---