

Rittal – The System.

Faster – better – everywhere.



PS 4339.000 Cable clamp rail

State: 5/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PS 4339.000 - Cable clamp rail Mounting angle for TS, PC, TP universal console, TS base/plinths

For TS, PC, TP universal console, base/plinths, as strain relief for cable entries.

Features

Model No.	PS 4339.000
Product description	Provides strain relief for cable entries. Depth-variable mounting in 25 mm hole pattern on the horizontal enclosure profile or in the TS base/plinth/Flex-Block.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Mounting tip	When mounting on a TS base/plinth, the fastening bolt for bases/plinths is required
Dimensions	Length: 1,785 mm Length: 70.3 "
Suitable for	Enclosure type: TS PC TP universal console Width: = 1,800 mm Enclosure type: TS PC TP universal console Width: = 70.9 "
Suitable for width	1,800 mm 70.9 "
Packaging unit	2 pc(s).
Net weight	9.61 kg
Gross weight	10.115 kg
Customs tariff number	73269098

Features

ECLASS 8.0

27400604

Product description

SZ Cable clamp rail (right angle section), for TS, PC, TP universal console, TS base/plinth, Flex-Block, for W: 1800 mm