

Rittal – The System.

Faster – better – everywhere.



TS 4579.000 Support Strip

State: 6/24/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4579.000 - Support Strip for VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



Features

Model No.	TS 4579.000
Product description	For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.
Technical specifications	4.5 mm diameter hole on a 25 mm hole pattern
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Length	790 mm 31.1 "
Suitable for door width	900 mm 35.4 "
Installation options VX SE	In door width 900 mm In enclosure width 800 mm, on the inner mounting level
Installation options AX	In enclosure width 800 mm, in conjunction with rail for interior installation AX and base configuration rail for AX
Installation options AX stainless steel	In enclosure width + 800 mm In door width 800 mm, in conjunction with the punched door strip
Installation options TS	In enclosure width/depth 800 mm, on the inner mounting level

Features

Installation options TP	In TP pedestal and one-piece console pedestal width 800 mm, in conjunction with rail for interior installation for TP, compact enclosure HD
Suitable for	Enclosure type: TS VX SE TP AX Width/depth: 800 mm Enclosure type: TS VX SE TP AX Width/depth: 31.5 ~
Packaging unit	20 pc(s).
Net weight	8 kg
Gross weight	8.1 kg
PCF/VE (cradle-to-gate)	37.23 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	TS support strip, for TS, VX SE, TP, for inner mounting level: for W/D: 800 mm, for door width: 900 mm, L: 790 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------