


# Rittal – The System.

Faster – better – everywhere.



## SZ 4943.000

## C rails 30/15

State: 6/10/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 4943.000 - C rails 30/15 to EN 60 715 for VX, TS, VX SE

For direct mounting on the horizontal enclosure profile or vertical enclosure profile using additional fastening components.



## Features

Model No.	SZ 4943.000
Material	Carbon steel
Surface finish	Zinc-plated
Length	455 mm 17.9 "
Installation options	<p>On the inner mounting level, on VX enclosure profile</p> <p>On the vertical TS, VX SE enclosure section via snap-on nuts TS 8800.808 or adapter rail for VX compatibility</p> <p>On the horizontal VX SE enclosure profile in the width bottom and top</p> <p>On the horizontal VX SE enclosure section in depth at the bottom (without mounting plate) and at the top using snap-on nut 8800.808</p> <p>On the horizontal TS enclosure section</p> <p>In the width or depth of the 3-part AX. Depending on the installation situation, the rail must be shortened to the desired length.</p>

# Features

---

Suitable for	Enclosure type: VX TS AX wall-mounted housing, 3-part Width/depth: 500 mm Enclosure type: VX TS AX wall-mounted housing, 3-part Width/depth: 19.7 "
Packaging unit	6 pc(s).
Net weight	1.8 kg
PCF/VE (cradle-to-gate)	9.11 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC000386
ETIM 8	EC000386
ECLASS 8.0	27400602
Product description	SZ C rail 30/15 to EN 60 715, for TS, SE, for W/D: 500 mm, L: 455 mm

# Approvals

---

Explanations	PCF-declaration
--------------	-----------------