## Rittal - The System.

Faster - better - everywhere.





# CM 5001.214 Gland plate

State: 10/27/2025 (Source: rittal.com/us-en)



## CM 5001.214 - Gland plate for TP

Equipotential bonding is provided via fastening components and grounding points.

#### **Features**

Model No.	CM 5001.214		
Product description	Equipotential bonding is provided via assembly components and grounding points.		
Material	Carbon steel		
Surface finish	Zinc-plated		
Supply includes	Assembly components		
Note	For greater stability and universal cable entry, the base opening is divided in the width for 1000, 1200 and 1600 mm wide enclosures, and is suitable for various configurations.  Several base plate modules need to be combined to close off the base completely in the TS-IT		
Dimensions	Depth: 100 mm Depth: 3.94 "		
Suitable for	Enclosure type: TS IT TS CM TP Width: = 600 mm Enclosure type: TS IT TS CM TP Width: = 23.6 "		
Packaging unit	1 pc(s).		
Net weight	0.79		
Gross weight	0.813		
Customs tariff number	94039910		
EAN	4028177523180		

© Rittal 2025

#### **Features**

E-Number Sweden	E3404482	
ETIM 9	EC002620	
ETIM 8	EC002620	
ECLASS 8.0	27189261	

© Rittal 2025 3