

Rittal – The System.

Faster – better – everywhere.



VX 5301.337

Gland plate set, multi-piece, solid

State: 6/9/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.337 - Gland plate set, multi-piece, solid for VX IT

Multi-piece gland plate set consisting of solid gland plate modules and sliding panel for cable entry.

Features

Model No.	VX 5301.337
Product description	Multi-piece gland plate set consisting of solid gland plate modules and sliding panel for cable entry. The solid gland plate modules, depth 237.5 mm, can be optionally exchanged for a gland plate module with cable entry.
Benefits	The sequence of individual modules can be freely selected.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Base Plate Kit Sealing tape Assembly components 1 gland plate module, solid, depth: 75 mm 2 gland plate modules, closed, depth: 237.5 mm 1 sliding panel, depth 115 mm
Suitable for	Enclosure type: VX IT Width: = 800 mm Depth: = 800 mm Enclosure type: VX IT Width: = 31.5 " Depth: = 31.5 "
Packaging unit	1 pc(s).
Net weight	6.42 kg
Gross weight	6.44 kg
PCF/VE (cradle-to-gate)	24.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910

Features

ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	VX IT gland plate module, multi-piece, solid, for width 800 mm, W x D 800 x 800 mm, sheet steel
