Rittal – The System.

Faster – better – everywhere.



IT 5302.042

19" cable bridge, variable depth

State: 11/6/2026 (Source: www.rittal.com/us-en)

IT 5302.042 - 19" cable bridge, variable depth

Within the 19" assembly level, the cable bridge offers an integrated option for cable entry, between the front and rear assembly level within a cabinet.

Features

Model No.	IT 5302.042
Product description	A user-friendly way of creating integrated cable routing between the front and rear 19" mounting levels within the enclosure.
Benefits	Cable entry on the front via brush strip to the thermal partitioning of the cable entry area Direct cable routing between patch level and component for rear-side expansion, optimal cable routing for rear-side switch assembly Fully depth-variable with versatile, infinitely adjustable extension of the cable link Prevents incorrect airflow by partitioning the transition Open at the top for easy retrofitting, even with cables already inserted Cable bridge can be expanded upward by 1 U, thanks to the use of another cable feedthrough panel with brush strip
Material	Carbon steel Brush strip: Plastic, UL 94-V0
Surface finish	Spray-finished
Color	RAL 9005
Supply includes	Cable bridge Brush strip
Installation options	For attaching between the front and rear 19" mounting level
Distance between levels	500 - 750 mm 19.7 - 29.5 ″
Height units	1 U
Load capacity, static	150 N
Suitable for	for enclosure-independent mounting
Note	Order fastening material separately

Features

Packaging unit	1 pc(s).
Net weight	6.8 kg
Gross weight	7.239 kg
PCF/VE (cradle-to-gate)	PCF-Wert 18,78 kg Co² e
Customs tariff number	73269098
Product description	19" cable bridge, variable depth, 500-750 mm, RAL 9005