Rittal – The System.

Faster – better – everywhere.





IT 5302.042 19" cable bridge, variable depth

State: 11/26/2025 (Source: rittal.com/us-en)



IT 5302.042 - 19" cable bridge, variable depth

Within the 482.6 mm (19") mounting level, the cable link provides an integrated cable routing option between the front and rear mounting levels inside an enclosure.

Features

Model No.	IT 5302.042
Benefits	Cable entry at the front via brush strip for thermal partitioning of the cable entry zone Direct cable routing between the patch level and component with rear installation, optimum cable routing with switch mounted at the rear Fully depth-variable with versatile, infinitely adjustable extension of the cable link Prevents incorrect airflow by partitioning the transition Open at the top for easy retrofitting, even with cables already inserted Cable link extendible upwards by 1 U, by using an additional cable entry panel with brush strip
Material	Carbon steel Brush strip: Plastic, UL 94-V0
Surface finish	Spray-finished
Color	RAL 9005
Supply includes	Cable link Brush strip
Installation options	For attaching between the front and rear 19" mounting level
Distance between levels	500 - 750 mm 19.7 - 29.5 ″
Height units	1 U
Load capacity, static	150 N
Suitable for	for enclosure-independent mounting
Note	Assembly parts should be ordered separately
Packaging unit	1 pc(s).

© Rittal 2025

Features

Customs tariff number

73269098

© Rittal 2025 3