


Rittal – The System.

Faster – better – everywhere.



DK 5302.202

Cable entry panel with brush strip

State: 6/9/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.202 - Cable entry panel with brush strip

482.6 mm (19")

With cut-out 390 x 60 mm when using two opposite panels (2 U) or 390 x 30 mm for one panel (1 U) with brush insert.



Features

| | |
|---------------------|--|
| Model No. | DK 5302.202 |
| Product description | For convenient, simple cable routing between two areas separated by an imperial mounting level, e.g. between the front and rear areas of the 19" mounting level. |
| Benefits | Two panels can simply be combined with one another to make the cable gland bigger |
| Applications | For locking and simultaneous cable routing in installation zones to the 1 U, 482.6 mm (19") mounting standard |
| Material | Carbon steel Brush strip: Plastic, UL 94-HB, halogen-free Brush strip fibers: plastic PA6, halogen-free Fixing body brush strip: plastic PVC, halogenated |
| Surface finish | Spray-finished |
| Color | RAL 9005 |
| Mounting cut-out | Width:390 mm Height:30 mm Width:15.4 " Height:1.18 " |

Features

| | |
|-------------------------------------|--|
| Dimensions | Width: 482.6 mm Width: 19 " |
| Height units | 1 U |
| Packaging unit | 1 pc(s). |
| Net weight | 0.2 kg |
| Gross weight | 0.243 kg |
| PCF/VE (cradle-to-gate) | 0.9 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC000322 |
| ECLASS 8.0 | 27400604 |
| Product description | Cable gland panel with brush strip, 1 U, 482.6 mm (19"), sheet steel, RAL 9005 |