

Rittal – The System.

Faster – better – everywhere.



DK 5501.480 Slide Rails, 1U, Depth-Variable

State: 6/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.480 - Slide Rails, 1U, Depth-Variable for VX IT, TE, TX CableNet

For mounting between a front and a rear mounting level .



Features

Model No.	DK 5501.480
Benefits	Tool-free, time-saving one-person assembly from the front of the enclosure All three mounting holes in the EIA system punchings are available for screw-fastening the equipment Alternatively, direct screw fastening in the TE 8000 to the 482.6 mm (19") system punchings is also possible
Applications	For assembly on the front mounting level To support heavy installed equipment. To adapt to individual distances between 19" levels
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options	482.6 mm (19") L-profile rails, front and rear 482.6 mm (19") mounting frames, front and rear 19" standard profile rails in VX IT
Load capacity	1500 N
Note	Effective contact surface 25 mm per side

Features

Suitable for	Enclosure type: TS IT VX IT TE TX CableNet
Distance between levels	600 - 900 mm 23.6 - 35.4 "
Packaging unit	2 pc(s).
Net weight	3.2 kg
Gross weight	3.74 kg
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Slide rail, support surface Width: 25 mm, depth-variable, 150 kg, For two 482.6 mm (19") attachment level (front+rear), distance between levels:: 600-900 mm