

Rittal – The System.

Faster – better – everywhere.



DK 5501.480

Slide Rails, 1U, Depth-Variable

State: 8/7/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.480 - Slide Rails, 1U, Depth-Variable for VX IT, TE, TX CableNet

For mounting between a front and a rear mounting level .



Features

Model No.	DK 5501.480
Benefits	<p>Tool-free, time-saving one-person assembly from the front of the enclosure</p> <p>All three mounting holes in the EIA system punchings are available for screw-fastening the equipment</p> <p>Alternatively, direct screw fastening in the TE 8000 to the 482.6 mm (19") system punchings is also possible</p>
Applications	<p>For assembly on the front mounting level</p> <p>To support heavy installed equipment.</p> <p>To adapt to individual distances between 19" levels</p>
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options	<p>482.6 mm (19") L-profile rails, front and rear</p> <p>482.6 mm (19") mounting frames, front and rear</p> <p>19" standard profile rails in VX IT</p>
Load capacity	1500 N
Note	Effective contact surface 25 mm per side

Features

Suitable for	Enclosure type: TS IT VX IT TE TX CableNet
Distance between levels	600 - 900 mm 23.6 - 35.4 ~
Packaging unit	2 pc(s).
Net weight	3.2
Gross weight	3.74
Customs tariff number	73269098
EAN	4028177679030
E-Number Sweden	E7239697
ETIM 9	EC002620
ECLASS 8.0	27189261