Rittal – The System.

Faster – better – everywhere.



DK 5502.305

Drawer

State: 11/11/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 5502.305 - Drawer for a 482.6 mm (19") mounting level

Mounted on the front of profile rails, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts.

Features

Model No.	DK 5502.305
Product description	Mounted on the front of 482.6 mm (19") profile rails. Drawer includes cover and telescopic slides and can accommodate operating manuals and small parts. The smaller 2 U version is also suitable for mounting in a pivoting frame.
Material	Carbon steel
Color	RAL 9005
Supply includes	Fully assembled Security lock 12321
Clearance depth	419 mm 16.5 ″
Clearance width	411 mm 16.2 ″
Packaging unit	1 pc(s).
Net weight	6.406 kg
Gross weight	6.9 kg
PCF/VE (cradle-to-gate)	25.7 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261

Features

Product description	DK Drawer, 2 U, For a 482.6 mm (19") attachment level, Installation depth: 427 mm, RAL 9005