Rittal – The System.

Faster – better – everywhere.





DK 5502.325 Drawer

State: 11/15/2025 (Source: rittal.com/us-en)



DK 5502.325 - Drawer for a 482.6 mm (19") mounting level

Mounted on the front of profile rails, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts.

Features

Model No.	DK 5502.325
Product description	Mounted on the front of 482.6 mm (19") profile rails. Drawer includes cover and telescopic slides and can accommodate operating manuals and small parts. The smaller 2 U version is also suitable for mounting in a pivoting frame.
Material	Carbon steel
Color	RAL 9005
Supply includes	Fully assembled Security lock 12321
Clearance depth	419 mm 16.5 ″
Clearance width	411 mm 16.2 ″
Packaging unit	1 pc(s).
Net weight	7.785
Gross weight	8.195
PCF/VE (cradle-to-gate)	31.2 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177679399
E-Number Sweden	E7239796
ETIM 9	EC002620

© Rittal 2025

Features

ECLASS 8.0

27189261

© Rittal 2025 3