

Rittal – The System.

Faster – better – everywhere.



DK 5502.510 Gland plate

State: 11/19/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.510 - Gland plate for VX IT, TS IT, TX CableNet

Potential equalization via assembly components and grounding points are available . The base plate is set to cover the entire base opening.

Features

Model No.	DK 5502.510
Version	Base plate, solid, with sliding panel, multi-piece
Product description	Equipotential bonding is provided via fastening components and grounding points. Base Plate Kit: To conceal the entire base opening. Base plate modules: Select modules in keeping with the application.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Suitable for	Enclosure type: TS IT Width: 800 mm Depth: 600 mm Enclosure type: TS IT Width: 31.5 " Depth: 23.6 "
Packaging unit	1 pc(s).
Net weight	4.776
Gross weight	5.027
Customs tariff number	94039910
EAN	4028177682610
E-Number Sweden	E7239567
ETIM 9	EC002620
ECLASS 8.0	27189261