

Rittal – The System.

Faster – better – everywhere.



DK 5502.560 Gland plate

State: 7/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.560 - Gland plate for VX IT, TS IT, TX CableNet

Potential equalization via assembly components and grounding points are available . The base plate is set to cover the entire base opening.

Features

Model No.	DK 5502.560
Version	Base plate, solid, with sliding panel, multi-piece
Product description	Equipotential bonding is provided via fastening components and grounding points. Base Plate Kit: To conceal the entire base opening. Base plate modules: Select modules in keeping with the application.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Note	To select the required module plates for completing the base area, please observe the information about the base mount included in the assembly instructions.
Suitable for	Enclosure type: TS IT Width: 600 mm Depth: 1,200 mm Enclosure type: TS IT Width: 23.6 " Depth: 47.2 "
Packaging unit	1 pc(s).
Net weight	6.582 kg
Gross weight	6.928 kg
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Gland plate Set, WxD: 600x1200 mm, For TS IT, solid, multi-piece