Rittal - The System.

Faster – better – everywhere.





DK 5528.120 TS IT Network/Server Enclosure

State: 12/9/2025 (Source: rittal.com/us-en)



DK 5528.120 - TS IT Network/Server Enclosure with glazed door, with 19" profile rails

TS IT is sealed for direct enclosure-specific climate control. 482.6 mm (19") interior installation with depth-variable 482.6 mm (19") profile rails for a load capacity of up to 1,500 kg, available in a range of size variants.



Features

| Model No. | DK 5528.120 | |
|----------------|---|--|
| Material | Carbon steel | |
| | Aluminum | |
| | Viewing door: Single-pane safety glass, 3 mm | |
| Surface finish | Enclosure frame: Dipcoat-primed | |
| | Interior installation: Dipcoat-primed | |
| | Doors and roof: Dipcoat-primed, powder coated | |
| General color | RAL 7035 | |
| Color | Housing frame and panels: RAL 7035 | |
| | Interior installation: RAL 9005 | |

© Rittal 2025 2

Features

| Supply includes | Enclosure frame TS 8 with doors and roof plate Glazed aluminum door, front, 180° hinges |
|---|--|
| | Lock front and rear: Comfort handle for semi-cylinders and security |
| | lock 3524 E |
| | Two 482.6 mm (19") mounting sections front and rear, variably |
| | mounted on support strips with quick-release fasteners |
| | Spacers, height 50 mm, for raising the cover plate above the fan |
| | breakout in the roof panel, for passive ventilation (enclosed) Not required for variants without cutout. |
| | Connection accessories for potential equalization with earthing point (supplied loose) |
| | 12 x 19" fasteners 1 U, contacting (supplied) |
| | 50 multi-tooth screws, conductive (supplied loose) |
| | IPPC pallet |
| | Roof plate, multi-piece, removable, with side cable entry in the depth |
| | and covered cut-out for fan mounting plate |
| | Carob steel door rear, closed, vertically divided, 180° hinges |
| Dimensions | Width: 600 mm |
| | Height: 1,800 mm |
| | Depth: 800 mm |
| | Width: 23.6 " |
| | Height: 70.9 " |
| | Depth: 31.5 " |
| Height units | 38 U |
| Height units | 38 U |
| Mounting space to 19" level, front/rear | 84 mm / 168 mm |
| Distance between levels as | 545 mm |
| delivered | 21.5 ″ |
| Design doors | Solid |
| Design of 19" mounting level(s) | Profile rails, 482.6 mm (19") |
| Load capacity | 15,000 N |
| Note | The door-opening angle may vary depending on site requirements or applications |
| Base material | Carbon steel |

© Rittal 2025 3

Features

| Packaging unit | 1 pc(s). |
|-----------------|---------------|
| Net weight | 83.6 |
| Gross weight | 88 |
| EAN | 4028177702738 |
| E-Number Sweden | E7239842 |
| ETIM 9 | EC002499 |
| ECLASS 8.0 | 27180207 |

Approvals

| Approvals | UL + C-UL (listed) |
|--------------|---------------------------|
| Certificates | Surface finish |
| Explanations | Declaration of conformity |

© Rittal 2025